

TYPE 12AQP-

The Du Mont Type 12AQP— is a 12 7/16-inch diameter, single beam, fast writing rate, electrostatic focus and deflection cathode-ray tube, suitable for high speed radar display. This tube features a specially-designed, low-drive electron gun permitting the use of transistorized video circuitry. The use of post acceleration allows maximum deflection sensitivity with high overall accelerating voltages. A special deflection structure is incorporated so that minimum spot defocusing is obtained with deflection.

The screen is aluminized for greater light output and to minimize screen charging effects.

GENERAL CHARACTERISTICS

Electrical Data

Focusing Method Deflecting Method			Electrostatic Electrostatic			
Direct Interelectrode Cap	acitances	, Approxir	mate			
Cathode to all				4.5		μμf
Grid No. 1 to all	Grid No. 1 to all			13.0		μμf
D1 to D2			4.6		μμf	
D3 to D4			2.2		μμf	
D1 to all other electrodes			14.0		μμf	
D2 to all other electrodes			14.0		μμf	
D3 to all other electro	D3 to all other electrodes			6.4		μμf
D4 to all other electro	D4 to all other electrodes			6.0		μμf
Modulation Electrode to all other electrodes			9.1		μμf	
Optical Data						
Phosphor Number	2	7	11	14	19	25
Fluorescent Color	Green	Blue	Blue	Blue	Orange	Orange
Phosphorescent Color	Green	Yellow		Orange	Orange	Orange
Persistence	Long	Long	Short	Long	Very Long (Note 1)	Very Long
Faceplate				Clear		

DE-6055 - 2 10/7/60

Allen B. Dy Mont Laboratories, hox Divisions of Fairchild Camera and Instrument Corp. Clitton, New Jersey



TYPE 12AQP-

GENERAL CHARACTERISTICS (Continued)

Mec	hani	ca	Data
-----	------	----	------

Overall Length Greatest Dlameter of Bulb Minlmum Useful Screen Dlameter	25 5/8 ± 3/8 12 7/16 ± 1/8 11.0	Inches Inches Inches
Bulb Contact	J1-22	Inches
Base	B14-38	
Basing	Special	
Base Alignment:	-	
D1D2 trace aligns with Pin No. 1 and tube axis	± 10	Degrees
Positive voltage on D1 deflects beam approximately	toward Base Pin No.	. 1
Positive voltage on D3 deflects beam approximately		
Bulb Contact Alignment:		
J1-22 Cap aligns with Pin Position No. 1	± 5	Degrees
J1-22 Cap aligns with D1D2 trace	± 5	Degrees
J1-22 Cap on same side as Pln No. 1		_
Trace Alignment:		
Angle between D3D4 and D1D2 traces	90 ± 1	Degrees

RATINGS (Design Center Values)

Heater Voltage	6.3	Volts
Heater Current at 6.3 Volts	$0.6 \pm 10\%$	Ampere
Post Accelerator Voltage	16, 000	Max. Volts DC
Accelerator Voltage	8,000	Max. Volts DC
Astigmatism Electrode Voltage	8,000	Max. Volts DC
Ratio Post Accelerator Voltage to Accelerator Voltage 2	2.0	
Focusing Electrode Voltage	3,000	Max. Volts DC
Modulation Adjustment Electrode	300	Max. Volts DC
Accelerator Input	6	Max. Watts
Grid No. 1 Voltage		
Negative Blas Value	300	Max. Volts DC
Positive Blas Value	0	Max, Volts DC
Positive Peak Value	0	Max. Volts
n.B. Dy Mont Laboratories, Incs	DE~6055 - 2	

Allen B. Dy Mont Laboratories, Inc. Divisions of Foirchild Camera and Instrument Corp. Clitton, New Jersey

FORM 809 BC-7-88-6H



TYPE 12AQP-

RATINGS (Design Center Values) (Continued)		
Peak Heater–Cathode Voltage Heater negative with respect to cathode During warm-up period not to exceed 15 seconds After equipment warm-up period Heater positive with respect to cathode	410 180 180	Max. Volts Max. Volts Max. Volts
Peak Voltage between Accelerator and any Deflection Electrode	1,500	Max, Volts
TYPICAL OPERATING CONDITIONS		
Post Accelerator Voltage ² Accelerator Voltage ² Astigmatism Electrode Voltage ³	10,000 5,000 5,000	Volts DC Volts DC Volts DC
Focusing Electrode Voltage ⁴ Grid No. 1 Voltage ⁵ Modulation Adjustment Electrode ⁶	1, 350 to 1, 650 -10 30 to 100	Volts DC Volts DC Max. Volts DC
Deflection Factors: D1D2 D3D4	95 to 105 81 to 90	Volts DC/Inch Volts DC/Inch
Modulation ⁷ Line Width "A" ⁴ Deflection Defocusing ⁸	10 .025	Max. Volts DC Max. Inch
Focusing Electrode Current for any operating condition Spot Position 9	~15 to +10 WithIn a 25→mm Sc	µA quare
MAXIMUM CIRCUIT VALUES		
Grid No. 1 Circuit Resistance Resistance in any Deflecting-Electrode Circuit ¹⁰	1.5 5.0	Max. Megohms Max. Megohms



TYPE K2007P-


TENTATIVE

NOTES

- 1. To avoid severe and permanent damage to the P19 screen when operating under static state conditions, it is recommended that the screen current not exceed 5 µADC.
- 2. This tube is designed for optimum performance when operating at an Eb3/Eb2 ratio of 2.0. Operation at other ratios of Eb3/Eb2 may result in changes in deflection uniformity and patter distortion.
- 3. The astigmatism electrode should be adjusted for optimum spot shape. For any necessary adjustment, its potential will fall within -300 to +300 volts with respect to the accelerator voltage.
- 4. For an 1b3 of 25 μADC, measured in accordance with MIL-E-1 specifications.
- 5. Visual extinction of undeflected, focused spot.
- 6. The modulation adjustment electrode is adjusted to obtain a Grid No. 1 voltage of -10 volts for the extinction of the undeflected, focused spot.
- 7. For an 1b3 of 45 µADC, measured in accordance with MIL-E-1 specifications.
- 8. The ratio of line width at 25 µA lb3 at maximum deflection to that at the center of the tube shall not exceed 1.5:1 using focusing and astigmatism correction.
- 9. With the free deflecting electrodes connected to the accelerator, and the tube shielded against external influences, the focused spot will fall within a 25-mm square centered with respect to the tube face and the square parallel to the traces produced by the deflection plate pairs.
- 10. It is recommended that the deflecting-electrode circuit resistances be approximately equal.

DE-6055

TENTATIVE



Allen B. Du Mont Laboratories, ioc. Divisions of Fairchild Camera and Instrument Corp. Clifton, New Jersey